

What is Hands Free?

The system comprises of a Hands Free Interface, a compatible reader (see specification table) and hands free keycards or keyfobs. The system operates by using the field being transmitted by the P series reader to wake up the token. This then communicates with the interface which contains a long range receiver.

The keycard increases this effective read range to typically 5 yds (maximum 50 yds). This is achieved by activating the system manually instead of using the reader field (maximum 8 feet)


Keycards also include a standard EM4100 proximity ID chip and can therefore be presented to any compatible proximity reader whether they are using the Hands Free interface or not.

The keycard has been designed with features to maximise battery life. These include a two second timeout once access has been granted and the prevention of repeated access requests whilst the keyfob remains in same reader field. Heavy usage or leaving the keycard within range of a reader will reduce battery life.

Interface Settings

To enable the buttons, the keycard must first be presented to the P series reader and then used in hands free mode. The keycard stores the details of this interface and can then activate the door using a button.

It can still be used in normal hands free mode and also in local passive mode with other standard readers.






The hands free interface has a pair of switches labelled SW2. Select either switch 1 or 2 to set which button the interface will respond to and then power cycle the interface to store this setting.

The keycard can store up to 60 doors, thirty for each button.

Battery replacement

Remove the screw on the back of the card. Open the case by inserting a flat head screw driver in the slot at the bottom of the card and gently prying the case open. Remove the circuit board and replace the batteries. Replace the circuit board, casing cover, screw and label.



Specifications

| Specifications | | | |
|-----------------------------|----------|--------------|----------------|
| Dimensions | | | |
| Width | 3 3/8 in | | |
| Height | 2 1/8 in | | |
| Depth | 3/8 in | | |
| System Specification | | | |
| Token type | EM4100 | | 125 kHz |
| Carrier frequency | | | 2.4 GHz |
| Environment | | | |
| Operating temperature | | 0 °C (32 °F) | 55 °C (131 °F) |

| Electrical | | | |
|----------------------------------|------------|---------|---------|
| Typical Battery Life | | 5 years | |
| Battery Type | 1 x CR2430 | | |
| Read range with hands free token | | | |
| With button - all readers | | | > 5 yds |
| P38 | | | 3 ft |
| P50 | | | 4 ft |
| P75 | | | 5 ft |
| P200 | | | 8 ft |
| P200E metal mount | | | 6 ft |
| Long range reader | | | 16 ft |

Handsfree Cards and Fobs have been tested to give a realistic representation of read ranges users can expect to see when taking into consideration different environmental factors.

| Results shown in meters only | | | | | | | |
|------------------------------|---------------|-----------|--------------------|----------------|-----------|--------------------|-----------------------------------|
| P Series readers | Handsfree Fob | | | Handsfree Card | | | Button Control: Handsfree Card |
| | On lanyard | In pocket | In pocket with GSM | On lanyard | In pocket | In pocket with GSM | |
| P38 | 0.20 | 0.10 | 0.00 | 0.40 | 0.30 | 0.00 | 20-25 |
| P50 | 0.30 | 0.20 | 0.15 | 0.50 | 0.40 | 0.30 | 20-25 |
| P75 | 0.50 | 0.30 | 0.30 | 0.80 | 0.50 | 0.40 | 20-25 |
| P200 | 1.30 | 0.80 | 0.40 | 1.80 | 1.00 | 0.50 | 20-25 |
| P200M | 1.30 | 0.80 | 0.40 | 1.80 | 1.00 | 0.50 | 20-25 |
| | 5.00 | 3.00 | 2.00 | 5.00 | 1.50 | 1.00 | 20-25 |

FCC Compliance

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

(1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.



+44 (0)1273 811011
support@paxton.co.uk
paxton.support



877.438.7298
supportUS@paxton-access.com
usapaxton.support



+31 (0)76 3333 999
support@paxton-benelux.com
paxton.benelux.support



+32 (0) 78485147
support@paxton-benelux.com
paxton.benelux.support



+49 (0) 251 2080 6900
verkauf@paxton-gmbh.de
paxton.gmbh.support



+33 (0)1 57 32 93 56
support@paxtonaccess.fr
paxton.support



+27 (0) 21 4276691
support@paxtonaccess.co.za
paxton.support



8000 3570 3783
support@paxtonaccess.ae
paxton.support



+52 55 5351 3667
soporte@paxton-access.com
paxton.soporte



+57 1508 8198
soporte@paxton-access.com
paxton.soporte



+44 (0)1273 811011
support@paxton.co.uk
paxton.support



Made in the UK

